


客户图

NO.	ECN NO.	DESCRIPTION	DATE
1		首次发行	



Note:

1: Material(材料):

Barrel: lead-free brass C6801 (针管: 无铅铜 C6801)

Plunger: lead-free brass C6801 (针头: 无铅铜 C6801)

Spring: SUS304 (弹簧: 不锈钢304)

2: Plating(电镀):

Barrel: 5u' Au over 200u' Cu over 200u' Ni

(针管: 镀金5u', 铜底200u', 镍底200u'.)

Plunger: 5u' Au over 200u' Cu over 200u' Ni

(针头: 镀金5u', 铜底200u', 镍底200u'.)

Spring: Gold plated (弹簧: 镀金)

3: Electrical(电气特性):

Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能):

Force: 100g $\pm$ 25g at working height. (100g $\pm$ 25g 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280 $\circ$ COperational Temperature: -40 $\circ$ C~ +85 $\circ$ C

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2023.9.2	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	$\pm 0.05\text{mm}$	X.XX	$\pm 0.50^\circ$
X.X	$\pm 0.10\text{mm}$	X.X	$\pm 1.00^\circ$
X.	$\pm 0.20\text{mm}$	X.	$\pm 2.00^\circ$

DESIGNED BY:		DWG. NO.	YZD0073-36086-02
CHECKED BY:		TITLE:	Pogo Pin
APPROVED BY:			