


A

E

Technical drawing of a G-switch. The drawing shows a side view of the device with a width of 19.50 and a height of 7.00. The label "G-Switch" is visible on the right side of the device.



B

C

- 1.Current rated: 1.5A
- 2.Voltage rating: 30V DC
- 3.Dielectric withstanding Voltage:500V AC
- 4.Contact resistance: 30mΩ Max
- 5.Insulation resistance: 1000MΩ Min
- 6.Operating temperature: -40°C ~ +85°C
- 7.Mating force: 35N Max
- 8.Unmating force: 10N Min

