


SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩMax
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩMin
Operation Temperature:-40℃ to +105℃

Contact Material: Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA66
Max.Processing Temp: 180℃ for 30-60 seconds
(230℃ for 10 seconds)

			GENE RL TOL E R A N C E		制 图 D R A W I N G	深 圳 市 富 港 科 技 有 限 公 司			
			D I M	T O L	审 核 C H E C K				
			X . X	± 0 . 3 0	批 准 A P P R O V A L	产 品 名 称 T I T L E	2 . 5 4 跳 线 帽 黑 色 (开 口 加 长 带 柄)	版 本 R E V .	A
1			X . X X	± 0 . 2 0	比 例 S C A L E	产 品 料 号 P A R T N O .	FG - M 2 5 4 - 1 - 1 3 5 - 0 P - B - G 0	单 位 U N I T S	mm
序 号 N o .	变 更 内 容 M O D I F Y C O N T E N T	日 期 M O D I F Y D A T E	A n g l e	± 3 . 0 °	投 影 P r o j e c t i o n	材 料 M A T E R I A L		页 次 S H E E T	1 / 1