





PCB Layout(Pattern side)

NO.1	
PART NO	vigor
2	130
3	180
4	250

NO.2	
PART NO	MATERIAL/QTY
S	SUS/1PC
D	SUS/2PCS

Note:

1.Operating force: 1st 100 $\pm$ 40gf
2st 250 $\pm$ 80gf2.Travel: 1st 0.25 $\pm$ 0.1mm
2st 0.40 $\pm$ 0.1mm

Circuit Diagram

⑤	Dust Cover	—	1	Kapton Film	Yellow	—
④	Terminal	—	4	Phosphor Bronze	Plating silver	—
③	Contact	—	2	F.Ag/SUS	Plating silver	—
②	Base	—	1	LCP	Black	—
①	Cover	—	1	SUS	Natural	—

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
------	-----------	---------	------	----------	-----------	--------

APPROVALS		DATE	
DRAWN	J.X.Zhang	2014/1/6	

CHECKED			TITLE:	TACT SWITCHES		
APPROVALS			PART NO.	K2-1835UL-A□□W		

TOLERANCES ARE	30~以上	± 0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	± 0.20				
	5~10	± 0.15				
	~ 5	± 0.10	$\pm 2'$	DRAWING NO.		SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			