









REACH & RoHS
COMPLIANT

REV.	ECN / DESCRIPTION	BY	DATE
A0	NEW	X.YAN	2024.10.22



NOTES:

MATERIAE

- HOUSING MATERIAL:PBT,COLOR IS GRAY
- CONTACT MATERIAL:BRONZE 0.46mm.
- PLATING:PLATING OVER NICKEL
- SHIELD:0.20mm THICKNESS COPPER ALLOYWITH NICKEL

ELECTRICAL:

- VOLTAGE RATING:125 VAC RM
- CURRENT RATING:1.5 AM
- CONTACT RESISTANCE:30 MILLIOHMS MAX.
- INSULATION RESISTANCE:500 MEGOHMS MIN @ 500V DC
- DIELECTRIC WITHSTANDI

RESISTANCE:500V AC RMS 50HZ.1MIN. MECHANICAL:

- DURRABILI :750 CYCLES MIN.
- PCB RETENTION PRE-SOLDER:1 LB MIN.

ENVIRONMENT AL:

- STORAGE: -40°C~+85°C
- OPERATION -40°C~+85°C

PART NUMBER	COLOR
R1188R53B	BLACK
R1188R53Y	YELLOW
R1188R53G	GRAY

CND-tek
磁联达

深圳磁联达电子有限公司
Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang
Community, Xili Street, Nanshan District, Shenzhen
E-mail: sales1@cd-tek.com 0755-27652992 29016433 Website:www.cd-tek.com

TITLE: 1*1 8P8C 53MINI 脚距11.43	SIZE A4	UNITS MM[INCH]	GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY: QG.CHEN
	PART NO.: R1188R53G	SACLE 1:1	REV A0	xÑ0.35 .xÑ0.30	CHECKED BY: SL.WANG
	REMARK:	SHEET 1/1		.xxÑ0.25 .xxxÑ0.10	DESIGND BY: X.YAN