










Applicable FPC




REV.	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
A			NEW DRAWING		

1. FPC NOT MATING CONDITION BANNED CLOSURE
2. ALL MATERIAL MUST BE COMPLY WITH ROHS
3. PART NO. LEGEND:

- ① .SERIES NAME: FPC 0.3PITCH H0.9 BACK FLIP TYPE CONNECTOR
- ② .CONTACT PIN NUMBER:**=CONTACT PIN NUMBER
- ③ .WELDING METHODS:1=SMT
- ④ .SHELLS MATERIALS/PLATING:
X=MEANINGLESS CODE
- ⑤ .MAIN COLOR:3=NATURAL COLOR
- ⑥ .CONTACT PLATING SPEC:
POINT OF PLATING:30=1u";
ALL GOLD PLATING:
20=1u";22=3u";23=5u";
TIN PLATING;06=ALL MATTE TIN
- ⑦ .PACKING SPEC: 3=CARRY TAPE

NO POSITIONS	A	B	C	D
9PIN	4.30	3.10	1.80	2.40
11PIN	4.90	3.70	2.40	3.00
13PIN	5.50	4.30	3.00	3.60
15PIN	6.10	4.90	3.60	4.20
17PIN	6.70	5.50	4.20	4.80
19PIN	7.30	6.10	4.80	5.40
21PIN	7.90	6.70	5.40	6.00
23PIN	8.50	7.30	6.00	6.60
25PIN	9.10	7.90	6.60	7.20
27PIN	9.70	8.50	7.20	7.80
29PIN	10.30	9.10	7.80	8.40
31PIN	10.90	9.70	8.40	9.00
33PIN	11.50	10.30	9.00	9.60
35PIN	12.10	10.90	9.60	10.20
39PIN	13.30	12.10	10.80	11.40
41PIN	13.90	12.70	11.40	12.00
45PIN	15.10	13.90	12.60	13.20
51PIN	16.90	15.70	14.40	15.00
55PIN	18.10	16.90	15.60	16.20
57PIN	18.70	17.50	16.20	16.80
61PIN	19.90	18.70	17.40	18.00
67PIN	21.70	20.50	19.20	19.80
71PIN	22.90	21.70	20.40	21.00



Recommended P.C.B Layout

NO.	COMPONENTS	MATERIALS	COLOR/SPECIFICATION	QUANTITY
1	HOUSING	LCP	BLACK UL94V-0	1 PCS
2	COVER	PA9T	BLACK UL94V-0	1 PCS
3	CONTACT	PHOSPHOR BRONZE	T=0.12mm PLATING	POSITIONS
4	CONTACT	PHOSPHOR BRONZE	T=0.12mm PLATING	POSITIONS
5	STATOR	BRASS	T=0.15mm PLATING	2 PCS

DESIGN:		Xiping Huang			广东国连电子有限公司									
CHECK:		Ke Tian			GUANGDONG GUOLIAN ELECTRONICS CO.,LTD									
APPROVED:		Youquan Xu		TITLE:										
DIM		TOL	DIM	TOL	0.3前插后掀H0.9									
X.		±0.25			PART NO.									
X. X		±0.20	X°	±3.0°	0309-GX-NPWB-GF-RH									
X. XX		±0.15	X. X°		REV. A		SCALE: N/A		UNIT: mm		SHEET: 1/1			
X. XXX			X. XX°											
			X. XXX°											