






Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)

SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20m Ω Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000M Ω Min
Operation Temperature:-40°c to +105°c

Contact Material:Copper Alloy
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Resistance To Soldering Heat:
260°C $\pm 5^{\circ}\text{C}$, 10s(PA6T&PA9T&LCP insulator)



P=With Post



默认 =W/O Post

Ordering Information

PM 254		- *	- N	- S	- *	- **	- *	- P
No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2=40Pin	Type 2=直針 4=彎針 8=彎針	Length (Plastic) (mm)	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin	Packing R=Reel +Cap (mm)	Post (mm)		

			GENERAL TOLERANCE		制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK	产品名称 TITLE	2.54双排 排母 贴片(塑高8.5)	版本 REV.	A
			X.X	± 0.30	批准 APPROVAL	产品料号 PART NO.	PM254-2-N-S-8.5-XX	单位 UNITS	mm
			X.XX	± 0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
			X.XXX	± 0.10	投影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	$\pm 3.0^{\circ}$					