





Materials

Pin (outer sleeve) :Brass,machined, CuZn38Pb2
Clip(contact 4 finger) : Beryllium copper,heat treated
Plating(outer sleeve) :
Tin plated : 1.25u"m/50u"nickel,5um/200u"Tin
Plating clip(contact):
1.25um/50 u"nickel,gold or tin plating
Insulator body(backend) : Glass filled thermoplastic polyester UL94V-0 electrical
Current rating : 3 Amps/contact max.
Contact resistance : 10mΩ /contact
Insulation resistance : 1000M at V=100V
Operating voltage : 60 AC/DC



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)





注：整条总长+0.8

Ordering Information

3622 28 1 XX R XX 095 01

Insulator Type
Code
1:Single row
2:Double row
No.of Pins
1-40Pin
Contact Plating
G0:Gold Flash
S0:Gold Flash/Tin
S1:3u"Gold/Tin
S2:5u"Gold/Tin
S3:10u"Gold/Tin
S4:15u"Gold/Tin
Length
095=9.5mm



JILN 深圳市锦凌电子有限公司
SHENZHEN JINLING ELECTRONIC CO.,LTD
Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892