





VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table				
PART NO	PIN	A	B	C
W20012K-4PW123	2*2	2.00	7.00	2.90
W20012K-6PW123	2*3	4.00	9.00	3.10
W20012K-8PW123	2*4	6.00	11.00	4.30
W20012K-10PW123	2*5	8.00	13.00	6.30
W20012K-12PW123	2*6	10.00	15.00	8.30
W20012K-14PW123	2*7	12.00	17.00	6.30
W20012K-16PW123	2*8	14.00	19.00	8.30
W20012K-18PW123	2*9	16.00	21.00	14.30
W20012K-20PW123	2*10	18.00	23.00	14.30
W20012K-22PW123	2*11	20.00	25.00	14.30
W20012K-24PW123	2*12	22.00	27.00	14.30
W20012K-26PW123	2*13	24.00	29.00	14.30
W20012K-28PW123	2*14	26.00	31.00	14.30
W20012K-30PW123	2*15	28.00	33.00	14.30
W20012K-32PW123	2*16	30.00	35.00	14.30
W20012K-44PW123	2*22	42.00	47.00	14.30

技术指标：

1. 温度范围：-25° C~+85° C.
2. 额定电压：250V AC, DC.
3. 耐电压：800V AC/minute.
4. 接触电阻：≤20mΩ .
5. 绝缘电阻：≥1000MΩ.
6. 额定电流：3A AC, DC.

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO. W20012K-XPW123	TITLE: PHB2.0 双排公头胶壳
.XX ±0.20	X.X° ±1°		
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	
		APPD: Sophia	
			SIZE A4
			UNITS MM
			SCALE N:A
			SHEET 1/1