




技术指标(Technical Index):

- 1. 工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2. 额定电压(Rated voltage):250V DC/AC.
- 3. 额定电流(Rated current):3.0A.
- 4. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5. 耐压值(Dielectricwithstanding voltage):800V AC/minute.
- 6. 绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 7. 适用线规(Apply to gauge):AWG#22~#28.

序号		品名		材质		
1		端子		Phosphor Bronze Bright tin plated		
GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd				
X.±0.50	±1°	PART NO. HMT-PHD2.0-GTDZ		TITLE: PA2.0(PHD)-WTB端子		
.X±0.20		DESIGN: James		CUSTOMER	SIZE	UNITS
.XX±0.10		CHED: Talen			A4	MM
MANUFACTURE DWG		APPD: Sophia			SCALE	SHEET
					N:A	1/1