










开关安装面板



电路示意图



端子可选择:

端子类型	螺丝脚	小焊脚	6.5插脚	4.8插脚
简图				

技术要求:

- 开关参数: 16(10)A 250VAC;20(12)A 125VAC
- 操作温度: -25℃~+85℃
- 接触电阻: $\leq 0.02 \Omega$
- 绝缘电阻: $\geq 1000M \Omega$
- 耐压:
极与极(P-P):1500Vac 50Hz 1min 1.0mA
极与壳(P-H):1500Vac 50Hz 1min 1.0mA
- 扭柄换向力: 2 — 1 5 N
- 寿命: 5 0 0 0 0 次
- 材料: 电胶木和铜合金

01	--	第一次出图		LKH		2024.04.07
版次 (REV.)	参考 (REF.)	描述 (DESCRIPTION)		绘图 (DRAW BY)	批核 (APP. BY)	日期 (DATE)
名称 (NAME)		CAX-KL-C223-YB-18.8JL		功能 (Function) DPDT: (ON)-OFF-(ON)		
型号 (MODEL NO.)		绘图 (DRAW BY) Laikunhua			批核 (APP. BY)	
物料编号 (Material No.)		比例 (SCALE) 1:1		日期 (DATE) 2024.04.07		日期 (DATE)
公差除特别要求外, 均按此规定执行: X. = ±0.20, X = ±0.15, XX = ±0.1, ≤ ±1°, 单位:mm (Tolerance unless otherwise specified: X. = ±0.20, X = ±0.15, XX = ±0.10, ≤ ±1°, unit:mm)					