











开关安装面板
(Switch panel hole dim.)




Handle choice:
手柄选择:

Handle type 手柄类型	Short handle 短手柄	Common handle 通用手柄	Long handle 长手柄
Diagram 简图			

Function choice:
功能选择:

NO.	specification 产品规格	function 功能
01	MTS102	SPDT: ON - ON
02	MTS112	SPDT: ON - (ON)
03	MTS103	SPDT: ON- OFF -ON
04	MTS113	SPDT: (ON)-OFF- ON
05	MTS123	SPDT: (ON)-OFF- (ON)



Specification(技术要求):

- Rated Load(额定负载): 2A 250VAC; 5A 125VAC
- Temperature Range(操作温度): -25℃~+85℃
- Contact Resistance(接触电阻): ≤0.02Ω
- Insulation Resistance(绝缘电阻): ≥1000MΩ
- Withstand Voltage(耐压): AC1500V/min
- Operating Force(操作力): 2—15N
- Life(寿命): 50000 times
- material(材料): 胶木 and Cu/Ep Ag(黄铜镀银)

01	--	第一次出图			2024.09.07
版次 (REV.)	参考 (REF.)	描述(DESCRIPTION)			日期 (DATE)
名称 (NAME)	Toggle Switch Specifications(钮子开关规格书)			功能 (Function)	See above(见上述)
型号 (MODEL NO.)	MTS Series CAX-MTS1**B2-BB-**JL			绘图 (DRAW BY)	批核 (APP. BY)
物料编号 (Material No.)	MTS102 103B1扁柄	比例 (SCALE)	NTS(见标注)	日期 (DATE)	2024.09.07
公差除特别要求外, 均按此规定执行: X.=±0.20, .X=±0.15, .XX=±0.1, <=±1°, 单位:mm (Tolerance unless otherwise specified: X.=±0.20, .X=±0.15, .XX=±0.10, <=±1°, unit:mm)					 