










电路示意图



开关安装面板



端子可选择:

端子类型	螺丝脚	小焊脚	6.5插脚	4.8插脚
简图				

技术要求:

- 开关参数: 16(10)A 250VAC; 20(12)A 125VAC
- 操作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 接触电阻: $\leq 0.02 \Omega$
- 绝缘电阻: $\geq 1000 \text{M}\Omega$
- 耐压:
 - 极与极(P-P): 1500Vac 50Hz 1min 1.0mA
 - 极与壳(P-H): 1500Vac 50Hz 1min 1.0mA
- 扭柄换向力: 2 — 1 5 N
- 寿命: 5 0 0 0 0 次
- 材料: 电胶木和铜合金

01	--	第一次出图	LKH		2024. 04. 07
版次 (REV.)	参考 (REF.)	描述 (DESCRIPTION)	绘图 (DRAW BY)	批核 (APP. BY)	日期 (DATE)
名称 (NAME)	钮子开关规格书		功能 (Function)	SPDT: (ON) - OFF - (ON)	
型号 (MODEL NO.)	CAX-KL-C123-YB-17.6JL		绘图 (DRAW BY)	Laikunhua	批核 (APP. BY)
物料编号 (Material NO.)		比例 (SCALE)	1:1	日期 (DATE)	2024. 04. 07
公差除特别要求外, 均按此规定执行: X. = ± 0.20 , . X = ± 0.15 , . XX = ± 0.1 , $\leq \pm 1^{\circ}$, 单位: mm (Tolerance unless otherwise specified: X. = ± 0.20 , . X = ± 0.15 , . XX = ± 0.10 , $\leq \pm 1^{\circ}$, unit: mm)					