










电路示意图



开关安装面板




端子可选择:

端子类型	螺丝脚	小焊脚	6.5插脚	4.8插脚
简图	 8.60	 $\phi 2.50$ 5.00	 $\phi 2.10$ 11.00 6.50	 $\phi 2.40$ 8.60 4.80

技术要求:

- 开关参数: 16(10)A 250VAC; 20(12)A 125VAC
- 操作温度: $-25^\circ\text{C} \sim +85^\circ\text{C}$
- 接触电阻: $\leq 0.02 \Omega$
- 绝缘电阻: $\geq 1000 \text{M}\Omega$
- 耐压:
 - 极与极(P-P): 1500Vac 50Hz 1min 1.0mA
 - 极与壳(P-H): 1500Vac 50Hz 1min 1.0mA
- 扭柄换向力: $2 - 1.5 \text{N}$
- 寿命: 50000次
- 材料: 电胶木和铜合金

01	--	第一次出图	LKH		2024.04.07
版次 (REV.)	参考 (REF.)	描述 (DESCRIPTION)	绘图 (DRAW BY)	批核 (APP. BY)	日期 (DATE)
名称 (NAME)		功能 (Function) SPDT:ON-ON			
型号 (MODEL NO.)	CAX-KL-C102-YB-17.0JL		绘图 (DRAW BY)	Laikunhua	批核 (APP. BY)
物料编号 (Material No.)	比例 1:1		日期 (DATE)	2024.04.07	日期 (DATE)
公差除特别要求外, 均按此规定执行: X. =±0.20, .X=±0.15, .XX=±0.1, <=±1°, 单位:mm (Tolerance unless otherwise specified: X. =±0.20, .X=±0.15, .XX=±0.10, <=±1°, unit:mm)					

浙江创都电子科技有限公司