



电路示意图



端子可选择:

端子类型	螺丝脚	小焊脚	6.5插脚	4.8插脚
简图				

技术要求:

1. 开关参数: 16(10)A 250VAC;20(12)A 125VAC
2. 操作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
3. 接触电阻: $\leq 0.02\ \Omega$
4. 绝缘电阻: $\geq 1000\text{M}\ \Omega$
5. 耐压:
极与极(P-P): 1500Vac 50Hz 1min 1.0mA
极与壳(P-H): 1500Vac 50Hz 1min 1.0mA
6. 扭柄换向力: 2 — 1 5 N
7. 寿命: 5 0 0 0 0 次
8. 材料: 电胶木和铜合金

01	—	第一次出图		LKH		2024.04.07
版次 (REV.)	参考 (REF.)	描述 (DESCRIPTION)		绘图 (DRAW BY)	批核 (APP. BY)	日期 (DATE)
名称 (NAME)		功能 (Function)		SPDT:ON-OFF		
型号 (MODEL NO.)		CAX-KL-C201-YB-18.2JL		绘图 (DRAW BY)	Laikunhua	批核 (APP. BY)
物料编号 (Material No.)		比例 (SCALE)	1:1	日期 (DATE)	2024.04.07	日期 (DATE)
公差除特别要求外，均按此规定执行: X. = ±0.20, .X = ±0.15, .XX = ±0.1, <= ±1°, 单位:mm (Tolerance unless otherwise specified: X. = ±0.20, .X = ±0.15, .XX = ±0.10, <= ±1°, unit:mm)						 
浙江创都电子科技有限公司						