








技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$.
3. 额定电压: 150V AC/DC.
4. 额定电流: 1.0A AC/DC (AWG#28).
5. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact, $\leq 40\text{m}\Omega$ Change allowed.
6. 绝缘电阻: $\geq 500\text{M}\Omega$.
7. 耐电压: 500V AC (Minute)



PCB WELDING DRAWING (TOLERANCE: ± 0.05)

型号	CKT	A	B
HMT-DF1.25-10P-LTR	2*5	12.50	5.00
HMT-DF1.25-12P-LTR	2*6	13.75	6.25
HMT-DF1.25-14P-LTR	2*7	15.00	7.50
HMT-DF1.25-16P-LTR	2*8	16.25	8.75
HMT-DF1.25-18P-LTR	2*9	17.50	10.00
HMT-DF1.25-20P-LTR	2*10	18.75	11.25
.....			
HMT-DF1.25-50P-LTR	2*25	(25*1.25)+6.25	(25*1.25)-1.25



4	1.25A型双排立式吸盖	LCP UL94V-0 本色
3	1.25A型双排立式胶芯	PA6T UL94V-0 本色
2	1.25A型双排立式焊片	黄铜/表面镀锡80u"Min, 镀镍30u"Min
1	1.25A型双排立式端子	黄铜/表面镀锡80u"Min, 镀镍30u"Min
序号	名称	数量

GENERAL TOLERANCES UNLESS SPECIFIED	
.X $\pm$ 0.30	X. $^{\circ}$ $\pm$ 5 $^{\circ}$
.XX $\pm$ 0.25	.X. $^{\circ}$ $\pm$ 1 $^{\circ}$
.XXX $\pm$ 0.15	
MANUFACTURE DWG	



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.	HMT-DF1.25-NP-LTR
DESIGN:	James
CHED:	Talen
APPD:	Sophia

TITLE: 1.25 Pitch A型(DF13) 双排立式业务图		
CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/1