






RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE




PIN number variable size comparison table

PART NO	PIN	A	B	C
W200120K-4PY2423	2*2	2.0	6.0	3.2
W200120K-6PY2423	2*3	4.0	8.0	3.2
W200120K-8PY2423	2*4	6.0	10.0	3.0
W200120K-10PY2423	2*5	8.0	12.0	5.0
W200120K-12PY2423	2*6	10.0	14.0	7.0
.....				
W200120K-44PY2423	2*22	42.0	46.0	39.0



2~3P结构样式

4P 结构样式



技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
- 工作温度: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
- 额定电压: 250V DC/AC(rms).
- 额定电流: 3.0A AC, DC.
- 接触电阻: $\leq 20\text{m}\Omega$.
- 耐压值: 800V AC/minute.
- 绝缘电阻: $\geq 1000\text{M}\Omega$.

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	± 0.30	X.°	$\pm 5^{\circ}$
.XX	± 0.20	X.X°	$\pm 1^{\circ}$
.XXX	± 0.10	X.XX°	$\pm 0.5^{\circ}$

MANUFACTURE DWG




深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
W200120K-XPY2423

TITLE:
PHB2.0MM A型双排弯针

DESIGN: James
CHED: Talen
APPD: Sophia



SIZE	UNITS
A4	MM
SCALE	SHEET
N:A	1/1