






版次	变更摘要	日期	序号	品名	材质
0	新产品发行	2019/03/27	①	1.0无盖卧式胶芯 (H=2.9)	LCP UL94V-0 黑色
			②	1.0无盖立式端子 (H=4.5)	铜合金/表面镀锡





CKT	DIM A	DIM B	DIM C
4	3.0	5.05	6.00
5	4.0	6.05	7.00
6	5.0	7.05	8.00
7	6.0	8.05	9.00
8	7.0	9.05	10.00
9	8.0	10.05	11.00
10	9.0	11.05	12.00
11	10.0	12.05	13.00
12	11.0	13.05	14.00
13	12.0	14.05	15.00
14	13.0	15.05	16.00
15	14.0	16.05	17.00
16	15.0	17.05	18.00
17	16.0	18.05	19.00
18	17.0	19.05	20.00
19	18.0	20.05	21.00
20	19.0	21.05	22.00
21	20.0	22.05	23.00
22	21.0	23.05	24.00
23	22.0	24.05	25.00
24	23.0	25.05	26.00
25	24.0	26.05	27.00
26	25.0	27.05	28.00
27	26.0	28.05	29.00
28	27.0	29.05	30.00
29	28.0	30.05	31.00
30	29.0	31.05	32.00



SECTION A-A



Applicable Flat Cable



- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -20° C~+85° C.
 3. 额定电压: 50V, AC(per pin)/DC等效.
 4. 额定电流: 0.5A.
 5. 接触电阻: ≤30mΩ.
 6. 绝缘电阻: ≥500MΩ.
 7. 耐压: 500V, AC/minute.
 8. 产品料号: 5001 - FWZ 10 45 - ** R 1 - B
- JM FPC CONNECTOR SERIES
PITCH: 1.0
HIGH: 4.5
- Standby
ALTERNATE
PACKING: R: 卷; T: 管
PIN



深圳市文章济美科技有限公司

品名 (TITLE)	1.0 Pitch 无盖立式正脚位 (H=4.5)	制图 (DR)	Anlan
料号 (DWG.NO)	5001-FWZ1045-**-R1-00-B	校对 (CHKD)	王涛
比例 (SCALE)	1:1	审核 (APPD)	黄志明
单位 (UNITS)	mm	张数 (SHEET)	1 OF 1
尺寸 (SIZE)	A4	REV	A

一般公差 (TOLERANCE)			
X ±0.50	.XX ±10		
X ±0.20	.XXX ±05		
ANGLES	±1°		