





Http://www.krhro.com



PCB Layout(Pattern Side)



LED colour(LED 颜色)	PART NO. (料号)
Red(红色)/Blue(蓝色)	K6-6151SM-23
Red(红色)/Jade green(翠绿)	K6-6151SM-27
Yellow(黄色)/Jade green(翠绿)	K6-6151SM-57
Blue(蓝色)/Jade green(翠绿)	K6-6151SM-37

- 1.Rating: 30mA DC30V
- 2.Contact resistance: $\leq 0.05\Omega$
- 3.Insulation resistance: $\geq 100M\Omega$
- 4.Operating Force: $260gf \pm 50gf$
- 5.Life: 100,000 Cycles
- 6.Salt mist Test: $12 \pm 1h$
- 7.Climate Grade: $-25^{\circ}C \sim 75^{\circ}C$

④	Cap	_____		PC	transparent	_____
③	Knob	_____		PPA	Porcelain White	_____
②	Terminal	_____		Copper alloy	Ag Plating	_____
①	Housing	_____		PPA	Black	_____
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 hro [®]		
DRAWN		LIANG	2026.04.25				
CHECKED					TITLE:	LED Tact Switch	
APPROVALS					PART NO.	K6-6151SM-□□	
TOLERANCES ARE	30 ^μ m 以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2°	DRAWING NO.	_____	SHEET 1 OF	

注：动作力和灯光可定制，此系列的贴片产品，不适用于整体回流焊焊接，需焊接开关后再带帽

			注：动作力和灯光可定制，此系列的贴片产品，不适用于整体回流焊焊接，需焊接开关后再带帽			
	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.