








ON STARTING POSITION
TOTAL TRAVEL POSITION



PCB LAND DIMENSION



CIRCUIT DIAGRAM

NOTE:

Rating: DC 12V 0.1A

Operating Force: 50 ± 15 gf

Lifetime: 50,000 Cycles

Travel: 0.60 ± 0.25 mm

⑤	Spring	—	1	SUS	Natural	—
④	Base	—	1	PA46	Black	—
③	Terminal	—	4	Phosphor Bronze	Ag Plated	—
②	Cover	—	1	SUS	Natural	—
①	KnOb	—	1	PA46	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN		LIUCAN		2020.12.18			
CHECKED						TITLE: DETECTOR SWITCHS	
APPROVALS						PART NO. K5-1217DA-02	
TOLERANCES ARE		30~以上	±0.30	ANGLE ±2'	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
					DRAWING NO. _____		SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.