






六方孔 2:1




电路切换图



产品型号	六方孔径尺寸(X)	齿轮颜色
6.5A	1.69±0.02	白色
6.5B	1.72±0.02	黑色
6.5C	1.74±0.02	黑色
6.5D	1.78±0.02	黄色
6.5E	1.76±0.02	红色

产品规格参数

额定负荷	DC 5V 0.5mA	适用温度	-25℃ -- +85℃	执子数	24点执子
机械寿命	200000cycles Min	适用湿度	≤85% +40℃	分解能	各相12脉冲/360°
电气寿命	100000cycles Min	耐焊接热	260±5℃ 3S	操作力	30±15gf.cm
绝缘电阻	>50MΩ DC50V 60S	接触电阻	≤10Ω		
耐压	AC50V 60S	可焊性	235±5℃ 3S		



线路板安装孔位置尺寸



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY :	DATE :	PART NAME:	
	陈一鸣	2014-02-23	编码器 贴片	
	CHECKED BY:	DATE :	PART NO.	HYCW04-6.5X-5P-S
	马跃	2014-02-23	MOLD NO.	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY:	DATE :	DRAW NO:	HYC-2607031647
	邱敏	2014-02-23	SHEET NO.	1 OF 1