








PCB Layout(Top view)



LED colour(LED 颜色)	Part No. (料号)
Whiler(白色)	K6-6280S-01
Red(红色)	K6-6280S-02
Blue(蓝色)	K6-6280S-03
Green(普绿)	K6-6280S-04
Yellow(黄色)	K6-6280S-05
Orange(橙色)	K6-6280S-06
Jade Green(翠绿色)	K6-6280S-07

NOTE:
Forcel: 680±100gf
Travel: 0.75±0.2mm
Life: 100,000 Cycles

CIRCUIT
WITH LEDCIRCUIT
WITHOUT LED

④	Terminal	—	2	Brass(0.3t)	—	—
③	Base	—	1	Fiberglass	—	—
②	Cover	—	1	SUS	—	—
①	Keystoke	—	1	Silica gel	Transparent	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIUCAN	2022.7.18					
CHECKED				TITLE:	LED Tact Switch		
APPROVALS				PART NO.	K6-6280S		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
		±2'	DRAWING NO.	_____		SHEET 1 OF 1	

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.