

NOTES:
MECHANICAL:
TOP CAGE: COPPER ALLOY, THICKNESS 0.25MM.
BOTTOM CAGE: STAINLESS STEEL SUS304, THICKNESS 0.25MM.
THIS CAGE IS FOR SINGLE SIDE USE ONLY.
TEMPERATURE:
OPERATION: -40°C~+85°C
STORAGE: -55°C~+105°C
RoHS COMPLIANCE.

