





回路图



安装孔位图

技术要求

1. 额定负荷: DC10V /1mA
2. 绝缘电阻: $\geq 100M \Omega$ DC50V;
3. 耐压: 50V AC/1min;
4. 使用温度: -20°C--+65°C;
5. 寿命: 100,000次。
6. 旋子扭力: 20gt $\pm$ 5

6	转 子	1	聚甲醛 (POM)	黑 色
5	外 壳	1	铁 皮 (SPCC)	镀铜锡
4	端 子	1	黄 铜 (Brass)	镀 银
3	底 座	1	尼龙 (PA66-GF30%)	黑 色
2	接 触 簧	1	磷铜 (PhosphorCopper)	t0.1mm
1	定 位 片	1	不锈钢 (Stainless Steel)/磷铜	t0.15mm
序 号	名 称	数 量	材 料	备 注



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2'$ X.X' $\pm 0.5'$ UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 编码器	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW05-9D-5P-DH
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2607011651
			SHEET NO.	1 OF 1