






ROHS

Http://www.krhro.com



Schematic(Shorting)



P.C.B layout

NO.1	
PART NO	H
K3-2530D-G3	3.0
K3-2530D-G4	4.0
K3-2530D-G5	5.0
K3-2530D-G6	6.0
K3-2530D-G7	7.0
K3-2530D-G8	8.0
K3-2530D-G9	9.0

⑦	Steel ball	—	1	Steel	—	—
⑥	Spring	—	5	Steel wire	—	—
⑤	Contact	—	2	Brass Strip	Ag Plated	—
④	Terminal	—	8	Brass Strip	Ag Plated	—
③	Base	—	1	NYLON	White	—
②	Cover	—	1	NYLON	White	—
①	Knob	—	1	NYLON	White	—

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
------	-----------	---------	------	----------	-----------	--------

APPROVALS			DATE	 hro®			
DRAWN	LIUCAN	2023.10.25					
CHECKED			TITLE:	TOGGLE SWITCHS			
APPROVALS			PART NO.	K3-2530D-G□			
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
			±2'	DRAWING NO.	_____	SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			