









NOTES:

1. MATERIAL:

1.1 HOUSING: PBT UL94V-0, BLUE(300C) ROHS

1.2 COVER: PBT UL94V-0, BLUE(300C) ROHS

1.3 4PIN CONTACTS: PHOSPHOR BRONZE C5191

1.4 5PIN CONTACTS: BRASS C2680

1.5 SHELL: SUS430

2. FINISH:

2.1 CONTACTS: GOLD G/F PLATED ON CONTACT AREA
80U" MIN. TIN PLATED ON SOLDER TAIL
50U" MIN. NICKEL UNDERPLATED OVERALL

2.2 SHELL: 50U" MIN. NICKEL PLATED

3. WAVE SOLDER CAPABLE TO 235°C±5°C

4. Operating Temperature: -25°C~+85°C

Pin Number	Signal Name	Pin Number	Signal Name
1	VBUS	10	VBUS
2	D-	11	D-
3	D+	12	D+
4	GND	13	GND
5	StdA_SSRX-	14	StdA_SSRX-
6	StdA_SSRX+	15	StdA_SSRX+
7	GND_DRAIN	16	GND_DRAIN
8	StdA_SSTX-	17	StdA_SSTX-
9	StdA_SSTX+	18	StdA_SSTX+
Shell	Shield		

CUSTOMER DRAWING

DRAWING
CHECK
APPROVAL

TOLERANCES ARE

30-150	±0.35	ANGLE ±3°
10-30	±0.2	
5-10	±0.15	
0-5	±0.1	

LAILAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO., LTD

TITLE	TYPE-A连接器9PINx2弯插L17.5 (卷口)	REV.	A
PART NO.	LAIL-TYPE-A-9PX2-01-WC	UNITS	mm
DWG.NO.		Projection	