

产品规格书

PRODUCT SPECIFICATION SHEET

物料名称

APPELLATION: A11 无线发射单线圈模组

MODE: YX-A11-R352825-G0840

客户料号

No.:

生产方	工艺审核 TECHNICAL	品质审核 QUALITY	项目审核 PROJECT	开发审核 DEVELOPING
	Jiuguijiang	wangxue	wangchunxia	Jiuguijiang


客户方	材料工程师 Materials Engineer	设计工程师 Engineer	主管审批 Approval	研发体系 R & D System



变更履历表

[illegible]

1. DIMENSIONS & MARKING:



中间的缺口尺寸：6*6MM

Symbol	A	B	C			
Value(mm)	35max	25max	40.00			

2. ELECTRICAL SPECIFICATIONS @25℃


- 2.1 Operating Temperature range: -40℃~+85℃
- 2.2 Storage temperature range: -25℃ TO +125℃
- 2.3 The test frequency: 100 KHz, 100mV @ 25℃,65%
- 2.4 OCL : 33.2±10% μH .
- 2.5 Diameter : 0.08*24P*1P
- 2.6 Turns Ratio: 28T

DRAWN BY:	CHECKED BY:	APPROVED BY:	CUSTOMER:
jiuguijiang	jiuguijiang	wangchunxia	PART NO. : YX-A11-R352825-G0840

3、 Bill of materials:

序号	物料名称	物料规格	材料使用	备注
1	丝包线	0.08*24*1P	√	
2	软磁片	35*25mm	√	
3	锡条	Sn97.3-0.7Cu	√	

4、 Packaging:



- 4.1 Quantity per grid: 20 PCS
- 4.2 Quantity per carton: 20*50 = 1000PCS
- 4.3 Quantity per carton: 1000*3 = 3000PCS
- 4.4 Carton size: 350*350*180mm.

DRAWN BY:	CHECKED BY:	APPROVED BY:	CUSTOMER:
jiuguijiang	jiuguijiang	wangchunxia	PART NO. : YX-A11-R352825-G0840
CND-TEK 深圳磁联达电子有限公司			REV. : A
			PAGE: 4 Of 4