



CIRCUIT DIAGRAM

Operation position



NOTE:
Rating: DC12V 0.1A
Operating Force: ≤40gf
Lifetime: 50,000 Cycles
Travel: 0.40±0.20mm

⑤	Spring	—	1	Phosphor bronze	Ag Plated	—
④	Base	—	1	PA	Black	—
③	Terminal	—	2	Brass	Ag Plated	—
②	Cover	—	1	Brass	Sn Plated	—
①	Knob	—	1	PA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIUCAN	2024.9.9					
CHECKED				TITLE:	DETECTOR SWITCHS		
APPROVALS				PART NO.	K5-1217SW-01		
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
		±2'		DRAWING NO.			SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			