



Schematic(Shorting)



NO.1	
PART NO	H
K3-2330D-G3	3.0
K3-2330D-G4	4.0
K3-2330D-G5	5.0
K3-2330D-G6	6.0
K3-2330D-G7	7.0
K3-2330D-G8	8.0
K3-2330D-G9	9.0

P.C.B layout

⑦	Steel ball	—	1	Steel	—	—
⑥	Spring	—	5	Steel wire	—	—
⑤	Contact	—	2	Brass Strip	Ag Plated	—
④	Terminal	—	8	Brass Strip	Ag Plated	—
③	Base	—	1	NYLON	White	—
②	Cover	—	1	NYLON	White	—
①	Knob	—	1	NYLON	White	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE				
DRAWN	LIUCAN	2023.10.25				
CHECKED			TITLE:	TOGGLE SWITCHES		
APPROVALS			PART NO.	K3-2330D-G□		
TOLERANCES ARE		30~0.1	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20	±2°	DRAWING NO.	PROJ:
		5~10	±0.15			
		~ 5	±0.10			SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			