

Rating:

7A 125V AC UL cUL

2.5A 250V AC VDE 3C KC

Insert And Extract Force: 1.36kgf~6.8kgf

Terminal Strength: $\geq 60N$

Operating Life: ≥ 6000 cycles

Withstand Voltage:





Between all terminals: 2500VAC (50-60Hz) 1min

Terminals to Base: 3750V AC (50-60Hz) 1min

Leakage Current: 1mA

Insulation Resistance: $\geq 100M\Omega$ 500V DC

Body Material: NYLON66 94V-2(0)



序号	名称	材料	处理	数量	备注
1	DB-6-1 塑料件	环阻PA66	黑色	1	
2	DB-6-N1L 圆针	黄铜	镀镍	1	
3	DB-8-1DX 圆针	黄铜	镀镍	2	
4	DB-6-P4 端子	黄铜	镀锡	1	
5	DB-6-P3 端子	黄铜	镀锡	2	

			GENERAL TOLERANCE		制图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核				
			X.X	± 0.30	批准	产品名称	DB-6 (电源插座)		版本
			X.XX	± 0.20	比例	产品料号	DB-6-1P4P3		REV.
			X.XXX	± 0.10	SCALE	PART NO.			UNIT
			Angle	$\pm 3.0^\circ$	投影	材料			mm
序号	变更内容	日期			投影	材料			页次
No.	MODIFY CONTENT	MODIFY DATE			Projection	MATERIAL			SHEET