







PC Board Layout



说明:

1. 材质: 胶芯: PBT, UL94V-0;
COLOR;BLACK
端子: C5191
外壳: C2680

2. 电镀说明: 端子: 镍底, 镀金G.F
外壳: 表面镀镍

3. 性能说明:

- 1) 电压: 150V AC RMS.
2) 额定电流: 1.5A.
3) 接触电阻: 40mΩ Max.
4) 绝缘电阻: 500MΩ MIN.
5) 绝缘耐压: 1000V AC.
6) 工作温度: -40° C TO +80° C.
7) 耐久性: 500 Mating Cycles MIN.

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO., LTD					
CHECKED:	DATE:	TITLE: RJ45-10P/8C 59A 弯插 带屏蔽 带灯左黄右绿 脚后3.05					
DRAWN: YKX	DATE: 2024-7-7	PART. NO.		R-RJ45R08P-C005			
		UNIT	mm	SCALE	free	⊕ ⊖	
		FILE NO.	Ckmtw-RJ45-0271	REV.	B	HY04	