








1. Material:see table A
2. Plating:see table A
3. Electrical characteristics
 - 3.1 Rated voltage:60V,50Hz,rms.
 - 3.2 Insulation resistance≥5,00MΩ;
 - 3.3 Dielectric withstanding voltage: 200V AC 1 Min;
 - 3.4 Contact resistance:
 - 3.4.1 Inner conductor≤20mΩ;
 - 3.4.2 Outer conductor≤20mΩ;
 - 3.5 Characteristic impedance:50Ω.
 - 3.6 VSWR:
 - ≤1.3 (DC~3GHz);
 - ≤1.4 (3~6GHz).
 - 3.7 Frequency range:DC~6GHz.
 - 3.8 100% OPEN,SHORT CIRCUIT TEST.
4. Environment
 - 4.1 Operating temperature range: -40°C~+90°C.
 - 4.2 Relative humidity: ≤95%(40°C±2°C)
 - 4.3 Product should meet HSF requirement;
- 5.Mark▼Dimensions are important control dimensions; Mark▽Dimensions are pivotal control dimensions.

3	HOUSING	1	LCP 680B,COLOR:BLACK,UL 94V-0	—
2	CONTACT	1	Brass C2680,Contact Area Plating Au 4 u" Min . The Other Area Plating Au Gold Flash,Ni Plating 50~150 u"	—
1	SHELL	1	Phosphor bronze C5191,Contact Area Plating Au 2 u" Min,The Other Area Plating Au Gold Flash,Ni Plating 50~150 u"	—
Item	component	Qt'y	Material/Treatment	Note

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
			X. X	±0.30	审 核	产品名称 TITLE	RF 天线座 H=0.6 (4代)	版本 REV.	A
			X. XX	±0.10	批 准				
			X. XXX	±0.10	比 例	产品料号 PART NO.	HC-RF-IPEX2020-04	单 位 UNITS	mm
			Angle	±3.0°	SCALE				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE			投 影	材料 MATERIAL		页 次 SHEET	1/1
					Projection				