





NOTE:

1. MATERIAL:


- ① 1.1. HOUSING: THERMOPLASTIC, COLOR: WHITE, UL 94V-0;
② 1.2. CONTACT: COPPER ALLOY, T=0.15mm;
③ 1.3. SHELL: COPPER ALLOY, T=0.15mm.

2. FINISH:

- 2.1. CONTACT: GOLD FLASH PLATED ON MATING AREA, GOLD FLASH ON SOLDER TAILS, NICKEL UNDER PLATED OVER OF THE ALL;
2.2. SHELL: GOLD FLASH ON THE ALL, NICKEL PLATED UNDER.
2.3. TEMPERATURE RANGE: -25° ~ +85°



RECOMMENDED PCB LAYOUT 1
(GENERAL TOLERANCE IS ±0.05)



RECOMMENDED PCB LAYOUT 2
(GENERAL TOLERANCE IS ±0.05)

			GENERAL TOLERANCE		制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK				
			X.X	±0.30	批准 APPROVAL	产品名称 TITLE	RF 天线座 (1代)	版本 REV.	A
			X.XX	±0.20	比例 SCALE	产品料号 PART NO.	HC-RF-IPEX0303-01	单位 UNITS	mm
			X.XXX	±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°					