





X	Y
1.0	24.5
1.2	24.5



PANEL CUT-OUT

Rating:

7A 125V AC UL cUL

2.5A 250V AC VDE 3C KC

Insert And Extract Force: 1.36kgf~6.8kgf

Terminal Strength: ≥60N

Operating Life: ≥6000 cycles

Withstand Voltage:

Between all terminals: 2500VAC (50-60Hz) 1min

Terminals to Base: 3750V AC (50-60Hz) 1min

Leakage Current: 1mA

Insulation Resistance: ≥100MΩ 500V DC

Body Material: PC 94V-2~0

序号	名称	材料	处理	数量	备注
1	DB-8-6B 塑料件	PC	黑色	1	
2	DB-8-S9 端子	黄铜	镀锡	2	
3	DB-8-3C 圆针	黄铜	镀镍	2	

GENERAL TOLERANCE			制图	深圳市华灿天禄电子有限公司			
DIM			TOL	审核	ShenzhenhuacantianluELECTRONICS CO.,LTD		
X.X			±0.30	批准	产品名称	DB-8 (电源插座)	版本
X.XX			±0.20	比例	TITLE		REV.
X.XXX			±0.10	SCALE	产品料号	DB-8-6BS9	UNIT
Angle			±3.0°	投影	PART NO.		mm
序号	变更内容	日期	投影	材料	材料	材料	页次
No.	MODIFY CONTENT	MODIFY DATE	Projection	MATERIAL	MATERIAL	MATERIAL	SHEET