

B

C

D

Houing model 主型号
(TG, TE, TP, ZG, ZE, ZC, DH, MG, ME)







Alignment key 键位
(G, A, B, C, J, L 详见表二)

Series 系列 (B, K, T, W, F, U.....)

Insert Configuration 针芯配置
(302, 305, 312.....详见表一)


Housing materia外壳材质 (C:铜镀珍珠铬 K:铜镀黑铬)

IP rating(when mated)/防水等级(插合时): IP68



建议面板开孔尺寸

Insert Configuration 针芯配置	302	303	304	305
Pin Number(View N) 针芯排列N向				
Pin Size 接触体直径 (mm)	0.5	0.5	0.5	0.35
Withstand voltage 耐电压 (V) (AC)	500	500	500	300
Rated Current 额定电流 (A)	7.0	7.0	5.0	5.0
Insulation resistance 绝缘电阻 (MΩ)	≥3000MΩ			
R(max) 接触电阻 (mΩ)	10	10	10	15

GENERAL TOLERANCE (UNLESS SPECIFIED)	绘图 DWN	Y.Z 2026.05.15				
$\leq 10 \pm 0.15$ $< 10 \sim \leq 20 \pm 0.25$ $< 20 \sim \leq 50 \pm 0.5$ Angle $\pm 1^\circ$	确认 CHK				品名 TITLE	00B系列板后安装孔型插座 4芯, 黄铜镀珍珠铬, 焊线式, IP68防护等级
	核准 APVD				品号 PART NO	C160201-00253
 视 角 THIRD ANGLE	单位 UNIT	MM	版本 REV	A	型号 DRAWING NO	MEG. 00. 304. CLLP
	尺寸 SIZE	A4	页码 SHEET	1 OF 1		