




ROHS Compliant

MAPX	MODIFICATION	DATE	DRAW	APPROVE
序号	品名	材质		
①	0.8 Pitch E型 单槽侧插BTB公座胶芯	LCP UL94 V-0,颜色:本色		
②	0.8 Pitch E型 单槽侧插BTB公座端子	铜合金/表面点镀金		



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

Part No	CKT	A	B	C	D
BTB0.835-4PWZDB5-GB42	2*2	0.80	2.35	3.35	2.60
BTB0.835-6PWZDB5-GB42	2*3	1.60	3.15	4.15	3.40
BTB0.835-8PWZDB5-GB42	2*4	2.40	3.95	4.95	4.20
BTB0.835-10PWZDB5-GB42	2*5	3.20	4.75	5.75	5.00
BTB0.835-12PWZDB5-GB42	2*6	4.00	5.55	6.55	5.80
BTB0.835-14PWZDB5-GB42	2*7	4.80	6.35	7.35	6.60
BTB0.835-16PWZDB5-GB42	2*8	5.60	7.15	8.15	7.40
BTB0.835-18PWZDB5-GB42	2*9	6.40	7.95	8.95	8.20
BTB0.835-20PWZDB5-GB42	2*10	7.20	8.75	9.75	9.00
BTB0.835-22PWZDB5-GB42	2*11	8.00	9.55	10.55	9.80
BTB0.835-24PWZDB5-GB42	2*12	8.80	10.35	11.35	10.60
BTB0.835-26PWZDB5-GB42	2*13	9.60	11.15	12.15	11.40
BTB0.835-28PWZDB5-GB42	2*14	10.40	11.95	12.95	12.20
BTB0.835-30PWZDB5-GB42	2*15	11.20	12.75	13.75	13.00
BTB0.835-32PWZDB5-GB42	2*16	12.00	13.55	14.55	13.80
BTB0.835-34PWZDB5-GB42	2*17	12.80	14.35	15.35	14.60
BTB0.835-36PWZDB5-GB42	2*18	13.60	15.15	16.15	15.40
BTB0.835-38PWZDB5-GB42	2*19	14.40	15.95	16.95	16.20
BTB0.835-40PWZDB5-GB42	2*20	15.20	16.75	17.75	17.00
.....	...	...	...	...	...
BTB0.835-80PWZDB5-GB42	2*40	31.20	32.75	33.75	33.00
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES				TITLE: 0.8 Pitch E型单槽侧插BTB公座业务图(单高3.5)	
DECIMALS:		ANGLES:		PAR	BTB0.835-XPWZDB5-GB42
X.: ± 0.50		$\pm 1^{\circ}$		DWN	Lucas
X.X: ± 0.20				CHKD	Ethan
X.XX: ± 0.10				APVD	Jacob
				SCALE: 1:1	UNIT: MM
				SIZE: A4	SHEET: 1F1
				CUSTOMER COPY	REV: A