







Part No	CKT	A	B	C	D
BTB0.829-6PLBDB6-MB42	2*3	4.30	2.80	1.60	3.40
BTB0.829-8PLBDB6-MB42	2*4	5.10	3.60	2.40	4.20
BTB0.829-10PLBDB6-MB42	2*5	5.90	4.40	3.20	5.00
BTB0.829-12PLBDB6-MB42	2*6	6.70	5.20	4.00	5.80
BTB0.829-14PLBDB6-MB42	2*7	7.50	6.00	4.80	6.60
BTB0.829-16PLBDB6-MB42	2*8	8.30	6.80	5.60	7.40
BTB0.829-18PLBDB6-MB42	2*9	9.10	7.60	6.40	8.20
BTB0.829-20PLBDB6-MB42	2*10	9.90	8.40	7.20	9.00
BTB0.829-30PLBDB6-MB42	2*15	13.90	12.40	11.20	13.00
BTB0.829-40PLBDB6-MB42	2*20	17.90	16.40	15.20	17.00
BTB0.829-50PLBDB6-MB42	2*25	21.90	20.40	19.20	21.00
BTB0.829-60PLBDB6-MB42	2*30	25.90	24.40	23.20	25.00
BTB0.829-70PLBDB6-MB42	2*35	29.90	28.40	27.20	29.00
BTB0.829-80PLBDB6-MB42	2*40	33.90	32.40	31.20	33.00
BTB0.829-90PLBDB6-MB42	2*45	37.90	36.40	35.20	37.00
BTB0.829-100PLBDB6-MB42	2*50	41.90	40.40	39.20	41.00

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:0.8 Pitch F型单槽立式BTB	
			每座业务图(单高2.9)	
DECIMALS:	ANGLES:		PAR	BTB0.829-XPLBDB6-MB42
X.:±0.50	±1°		DWN	Lucas
X.X:±0.20			CHKD	Ethan
X.XX:±0.10		APVD	Jacob	
		SCALE1:1	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:1F1
				REV:A

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
3. 额定电压: $50\text{V}, \text{AC}$.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$



东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co,Ltd



TITLE:0.8 Pitch F型单槽立式BTB
母座业务图(单高2.9)

PAR	BTB0.829-XPLBDB6-MB42
-----	-----------------------

DWN	Lucas	
-----	-------	--

CHKD	Ethan	
------	-------	--

APVD	Jacob	
------	-------	--

SCALE1:1	UNIT:MM	
----------	---------	---

SIZE:A4	SHEET:1F1	REV:A
---------	-----------	-------

REV:A