




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



Part No	CKT	A	B	C	D	E
BTB0.845-8PLBSB1-MB42	8	2.40	3.50	5.10	4.20	4.00
BTB0.845-10PLBSB1-MB42	10	3.20	4.30	5.90	5.00	
BTB0.845-12PLBSB1-MB42	12	4.00	5.10	6.70	5.80	
BTB0.845-14PLBSB1-MB42	14	4.80	5.90	7.50	6.60	
BTB0.845-16PLBSB1-MB42	16	5.60	6.70	8.30	7.40	
BTB0.845-18PLBSB1-MB42	18	6.40	7.50	9.10	8.20	
BTB0.845-20PLBSB1-MB42	20	7.20	8.30	9.90	9.00	8.00
BTB0.845-22PLBSB1-MB42	22	8.00	9.10	10.70	9.80	
BTB0.845-24PLBSB1-MB42	24	8.80	9.90	11.50	10.60	
BTB0.845-26PLBSB1-MB42	26	9.60	10.70	12.30	11.40	
BTB0.845-28PLBSB1-MB42	28	10.40	11.50	13.10	12.20	
BTB0.845-30PLBSB1-MB42	30	11.20	12.30	13.90	13.00	
BTB0.845-32PLBSB1-MB42	32	12.00	13.10	14.70	13.80	8.00
BTB0.845-34PLBSB1-MB42	34	12.80	13.90	15.50	14.60	
BTB0.845-36PLBSB1-MB42	36	13.6	14.70	16.30	15.40	
BTB0.845-38PLBSB1-MB42	38	14.40	15.50	17.10	16.20	
BTB0.845-40PLBSB1-MB42	40	15.20	16.30	17.90	17.00	
BTB0.845-44PLBSB1-MB42	44	16.80	17.90	19.50	18.60	8.00
BTB0.845-50PLBSB1-MB42	50	19.20	20.30	21.90	21.00	
BTB0.845-60PLBSB1-MB42	60	23.20	24.30	25.90	25.00	
BTB0.845-70PLBSB1-MB42	70	27.20	28.30	29.90	29.00	
BTB0.845-80PLBSB1-MB42	80	31.20	32.30	33.90	33.00	
BTB0.845-100PLBSB1-MB42	100	39.20	40.30	41.90	41.00	

序号	品名	材质
①	0.8 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0, 颜色: 黑色
②	0.8 Pitch双槽立式BTB母座端子	铜合金/表面点镀金
③	0.8 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0, 颜色: 黑色

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 0.8 Pitch双槽立式BTB母座业务图(单高4.5)
DECIMALS:	ANGLES:		PAR BTB0.845-XPLBSB1-MB42
X.: ± 0.50	$\pm 1^{\circ}$		DWN Lucas
X.X: ± 0.20			CHKD Ethan
X.XX: ± 0.10			APVD Jacob
CUSTOMER COPY		SCALE: 1:1	UNIT: MM
		SIZE: A4	SHEET: 1F1
			REV: A