



| High photosynthesis<br>合高(H) | The female<br>seat height<br>母座高(H1) | The male<br>seat height<br>公座高(H2) | Insertion<br>height<br>(H3) |
|------------------------------|--------------------------------------|------------------------------------|-----------------------------|
| 4.0                          | 3.0                                  | 1.0                                | 1.9                         |
| 4.5                          | 3.5                                  | 1.0                                | 1.9                         |
| 5.0                          | 3.0/4.0                              | 2.0/1.0                            | 1.9                         |
| 5.5                          | 3.5/4.5                              | 2.0/1.0                            | 1.9                         |
| 6.0                          | 4.0                                  | 2.0                                | 1.9                         |
| 6.5                          | 4.5                                  | 2.0                                | 1.9                         |
| 7.0                          | 3.0                                  | 4.0                                | 1.9                         |
| 7.5                          | 3.5                                  | 4.0                                | 1.9                         |
| 8.0                          | 4.0                                  | 4.0                                | 1.9                         |
| 8.5                          | 4.5                                  | 4.0                                | 1.9                         |



1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围:  $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ .
3. 额定电压:  $125\text{V}$ , AC.
4. 接触电阻:  $\leq 0.02\Omega$ .
5. 绝缘电阻:  $\geq 100\text{M}\Omega$

| Part No                 | CKT | A     | B     | C     | D     | E    |
|-------------------------|-----|-------|-------|-------|-------|------|
| BTB0.810-8PLBSB1-GB42   | 8   | 2.40  | 3.45  | 5.10  | 4.20  | 4.00 |
| BTB0.810-10PLBSB1-GB42  | 10  | 3.20  | 4.25  | 5.90  | 5.00  |      |
| BTB0.810-12PLBSB1-GB42  | 12  | 4.00  | 5.05  | 6.70  | 5.80  |      |
| BTB0.810-14PLBSB1-GB42  | 14  | 4.80  | 5.85  | 7.50  | 6.60  |      |
| BTB0.810-16PLBSB1-GB42  | 16  | 5.60  | 6.65  | 8.30  | 7.40  |      |
| BTB0.810-18PLBSB1-GB42  | 18  | 6.40  | 7.45  | 9.10  | 8.20  |      |
| BTB0.810-20PLBSB1-GB42  | 20  | 7.20  | 8.25  | 9.90  | 9.00  |      |
| BTB0.810-22PLBSB1-GB42  | 22  | 8.00  | 9.05  | 10.70 | 9.80  |      |
| BTB0.810-24PLBSB1-GB42  | 24  | 8.80  | 9.85  | 11.50 | 10.60 | 8.00 |
| BTB0.810-26PLBSB1-GB42  | 26  | 9.60  | 10.65 | 12.30 | 11.40 |      |
| BTB0.810-28PLBSB1-GB42  | 28  | 10.40 | 11.45 | 13.10 | 12.20 |      |
| BTB0.810-30PLBSB1-GB42  | 30  | 11.20 | 12.25 | 13.90 | 13.00 |      |
| BTB0.810-32PLBSB1-GB42  | 32  | 12.00 | 13.05 | 14.70 | 13.80 |      |
| BTB0.810-34PLBSB1-GB42  | 34  | 12.80 | 13.85 | 15.50 | 14.60 |      |
| BTB0.810-36PLBSB1-GB42  | 36  | 13.6  | 14.65 | 16.30 | 15.40 |      |
| BTB0.810-38PLBSB1-GB42  | 38  | 14.40 | 15.45 | 17.10 | 16.20 |      |
| BTB0.810-40PLBSB1-GB42  | 40  | 15.20 | 16.25 | 17.90 | 17.00 |      |
| BTB0.810-44PLBSB1-GB42  | 44  | 16.80 | 17.85 | 19.50 | 18.60 |      |
| BTB0.810-50PLBSB1-GB42  | 50  | 19.20 | 20.25 | 21.90 | 21.00 |      |
| BTB0.810-60PLBSB1-GB42  | 60  | 23.20 | 24.25 | 25.90 | 25.00 |      |
| BTB0.810-70PLBSB1-GB42  | 70  | 27.20 | 28.25 | 29.90 | 29.00 |      |
| BTB0.810-80PLBSB1-GB42  | 80  | 31.20 | 32.25 | 33.90 | 33.00 |      |
| BTB0.810-100PLBSB1-GB42 | 100 | 39.20 | 40.25 | 41.90 | 41.00 |      |



| 序号 | 品名                       | 材质                       |
|----|--------------------------|--------------------------|
| ①  | 0.8 Pitch双槽立式<br>BTB公座胶芯 | PA10T UL94 V-0,<br>颜色:黑色 |
| ②  | 0.8 Pitch双槽立式<br>BTB公座端子 | 铜合金/表面点镀金                |
| ③  | 0.8 Pitch双槽立式<br>BTB公座吸盖 | LCP UL94 V-0,<br>颜色:黑色   |

|                                       |         |                                                                                                                                                       |                                     |                                                                                       |       |
|---------------------------------------|---------|-------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------|---------------------------------------------------------------------------------------|-------|
| MANUFACTURE DWG                       |         |  <div>东莞市讯普电子科技有限公司<br/>DongGuan XunPu Electronics Co.,Ltd</div> |                                     |                                                                                       |       |
| UNLESS OTHERWISE SPECIFIED TOLERANCES |         |                                                                  | TITLE:0.8 Pitch双槽立式BTB公座产业条图(单高1.0) |                                                                                       |       |
|                                       |         |                                                                                                                                                       | PAR                                 | BTB0.810—XPLBSB1—GB42                                                                 |       |
|                                       |         |                                                                                                                                                       | DWN                                 | Lucas                                                                                 |       |
|                                       |         |                                                                                                                                                       | CHKD                                | Ethan                                                                                 |       |
| DECIMALS:                             | ANGLES: | APVD                                                                                                                                                  | Jacob                               |                                                                                       |       |
| X:±0.50                               | ±1°     | SCALE1:1                                                                                                                                              | UNIT:MM                             |  |       |
| X.X:±0.20                             |         |                                                                                                                                                       |                                     |                                                                                       |       |
| X.XX:±0.10                            |         | CUSTOMER COPY                                                                                                                                         | SIZE:A4                             | SHEET:1F1                                                                             | REV:A |