





High photosynthesis 高商(H)	The female seat height 母座高(H1)	The male seat height 公座高(H2)	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9



Part No	CKT	A	B	C	D	E
BTB0.840-8PLBSB1-GB42	8	2.40	3.45	5.10	4.20	4.00
BTB0.840-10PLBSB1-GB42	10	3.20	4.25	5.90	5.00	
BTB0.840-12PLBSB1-GB42	12	4.00	5.05	6.70	5.80	
BTB0.840-14PLBSB1-GB42	14	4.80	5.85	7.50	6.60	
BTB0.840-16PLBSB1-GB42	16	5.60	6.65	8.30	7.40	
BTB0.840-18PLBSB1-GB42	18	6.40	7.45	9.10	8.20	
BTB0.840-20PLBSB1-GB42	20	7.20	8.25	9.90	9.00	
BTB0.840-22PLBSB1-GB42	22	8.00	9.05	10.70	9.80	
BTB0.840-24PLBSB1-GB42	24	8.80	9.85	11.50	10.60	8.00
BTB0.840-26PLBSB1-GB42	26	9.60	10.65	12.30	11.40	
BTB0.840-28PLBSB1-GB42	28	10.40	11.45	13.10	12.20	
BTB0.840-30PLBSB1-GB42	30	11.20	12.25	13.90	13.00	
BTB0.840-32PLBSB1-GB42	32	12.00	13.05	14.70	13.80	
BTB0.840-34PLBSB1-GB42	34	12.80	13.85	15.50	14.60	
BTB0.840-36PLBSB1-GB42	36	13.6	14.65	16.30	15.40	
BTB0.840-38PLBSB1-GB42	38	14.40	15.45	17.10	16.20	
BTB0.840-40PLBSB1-GB42	40	15.20	16.25	17.90	17.00	
BTB0.840-44PLBSB1-GB42	44	16.80	17.85	19.50	18.60	
BTB0.840-50PLBSB1-GB42	50	19.20	20.25	21.90	21.00	
BTB0.840-60PLBSB1-GB42	60	23.20	24.25	25.90	25.00	
BTB0.840-70PLBSB1-GB42	70	27.20	28.25	29.90	29.00	
BTB0.840-80PLBSB1-GB42	80	31.20	32.25	33.90	33.00	
BTB0.840-100PLBSB1-GB42	100	39.20	40.25	41.90	41.00	



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: $125\text{V}, \text{AC}$.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$

序号	品名	材质
①	0.8 Pitch双槽立式 BTB公座胶芯	PA10T UL94 V-0, 颜色:黑色
②	0.8 Pitch双槽立式 BTB公座端子	铜合金/表面点镀金
③	0.8 Pitch双槽立式 BTB公座吸盖	LCP UL94 V-0, 颜色:黑色

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:0.8 Pitch双槽立式BTB公座业条图(单高4.0)	
			PAR	BTB0.840—XPLBSB1—GB42
			DWN	Lucas
			CHKD	Ethan
DECIMALS:	ANGLES:	APVD	Jacob	
X.:±0.50	±1°	SCALE1:1	UNIT:MM	
X.X:±0.20				
X.XX:±0.10		CUSTOMER COPY	SIZE:A4 SHEET:1F1 REV:A	