






SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PBT
Max.Processing Temp: 180°C for 30-60 seconds
(230°C for 10 seconds)

Ordering Information

HC-JP 254 - 1 - ** - 0P - * - **				
No.of Rows 1=Single Type	Length (mm) 45=4.5mm 60=6.0mm 65=6.5mm	Type OP=Open CL=Close	Color B=Black L=Blue R=Red W=White Y=Yellow	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
					审 核				
			X. X	±0.30	CHECK				
					批 准	产品名称	2.54 跳线帽 (开口)	版本	A
			X. XX	±0.20	APPROVAL	TITLE		REV.	
			X. XXX	±0.10		产品料号	HC-JP254-1-60-0P-B-XX	单位	mm
					比 例	PART NO.		UNITS	
序号	变更内容	日期	Angle	±3.0°	投 影	材料		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE	Projection			MATERIAL		SHEET	