

ROHS Compliant

MAPX




MODIFICATION

DATE

DRAW

APPROVE


Part No	CKT	A	B	C
BTB0.857-20PLBDB2-GB42	2*10	7.20	13.80	12.20
BTB0.857-22PLBDB2-GB42	2*11	8.00	14.60	13.00
BTB0.857-24PLBDB2-GB42	2*12	8.80	15.40	13.80
BTB0.857-26PLBDB2-GB42	2*13	9.60	16.20	14.60
BTB0.857-28PLBDB2-GB42	2*14	10.40	17.00	15.40
BTB0.857-30PLBDB2-GB42	2*15	11.20	17.80	16.20
BTB0.857-32PLBDB2-GB42	2*16	12.00	18.60	17.00
BTB0.857-34PLBDB2-GB42	2*17	12.80	19.40	17.80
BTB0.857-36PLBDB2-GB42	2*18	13.60	20.20	18.60
BTB0.857-38PLBDB2-GB42	2*19	14.40	21.00	19.40
BTB0.857-40PLBDB2-GB42	2*20	15.20	21.80	20.20
BTB0.857-42PLBDB2-GB42	2*21	16.00	22.60	21.00
BTB0.857-44PLBDB2-GB42	2*22	16.80	23.40	21.80
BTB0.857-46PLBDB2-GB42	2*23	17.60	24.20	22.60
BTB0.857-48PLBDB2-GB42	2*24	18.40	25.00	23.40
BTB0.857-50PLBDB2-GB42	2*25	19.20	25.80	24.20
.....	...	...	...	...
BTB0.857-200PLBDB2-GB42	2*100	79.20	85.80	84.20



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 100V, AC.
4. 接触电阻: $\leq 0.05\Omega$.
5. 绝缘电阻: $\geq 500\text{M}\Omega$

序号	品名	材质	MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
①	0.8 Pitch B型立式 BTB公座胶芯	LCP UL94 V-0, 颜色:本色	UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:0.8 Pitch B型立式BTB公座 业务图(单高5.7)		
②	0.8 Pitch B型立式 BTB公座端子	铜合金/表面点镀金				PAR	BTB0.857-XPLBDB2-GB42	
③	0.8 Pitch B型立式 BTB公座吸盖	不锈钢	DECIMALS:	ANGLES:		DWN	Lucas	
			X.:±0.50	±1°		CHKD	Ethan	
			X.X:±0.20			APVD	Jacob	
			X.XX:±0.10		CUSTOMER COPY	SCALE 1:1	UNIT:MM	
						SIZE:A4	SHEET:1F2	REV:A



MANUFACTURE DWG			东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:0.8 Pitch B型立式BTB公座 业务图(单高5.7)	
DECIMALS:	ANGLES:		PAR	BTB0.857-XPLDB2-GB42
X.:±0.50	±1°		DWN	Lucas
X.X:±0.20			CHKD	Ethan
X.XX:±0.10		APVD	Jacob	
		SCALE:1:1	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:2F2
				REV:A