









SECTION A-A



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

MAPX	MODIFICATION	DATE	DRAW	APPROVE
序号	品名	材质		
①	0.8 Pitch E型 单槽侧插BTB母座胶芯	LCP UL94 V-0, 颜色: 本色		
②	0.8 Pitch E型 单槽侧插BTB母座端子	铜合金/表面点镀金		

Part No	CKT	A	B	C	D
BTB0.851-4PWZDB5-MB42	2*2	0.80	2.45	3.60	2.60
BTB0.851-6PWZDB5-MB42	2*3	1.60	3.25	4.40	3.40
BTB0.851-8PWZDB5-MB42	2*4	2.40	4.05	5.20	4.20
BTB0.851-10PWZDB5-MB42	2*5	3.20	4.85	6.00	5.00
BTB0.851-12PWZDB5-MB42	2*6	4.00	5.65	6.80	5.80
BTB0.851-14PWZDB5-MB42	2*7	4.80	6.45	7.60	6.60
BTB0.851-16PWZDB5-MB42	2*8	5.60	7.25	8.40	7.40
BTB0.851-18PWZDB5-MB42	2*9	6.40	8.05	9.20	8.20
BTB0.851-20PWZDB5-MB42	2*10	7.20	8.85	10.00	9.00
BTB0.851-22PWZDB5-MB42	2*11	8.00	9.65	10.80	9.80
BTB0.851-24PWZDB5-MB42	2*12	8.80	10.45	11.60	10.60
BTB0.851-26PWZDB5-MB42	2*13	9.60	11.25	12.40	11.40
BTB0.851-28PWZDB5-MB42	2*14	10.40	12.05	13.20	12.20
BTB0.851-30PWZDB5-MB42	2*15	11.20	12.85	14.00	13.00
BTB0.851-32PWZDB5-MB42	2*16	12.00	13.65	14.80	13.80
BTB0.851-34PWZDB5-MB42	2*17	12.80	14.45	15.60	14.60
BTB0.851-36PWZDB5-MB42	2*18	13.60	15.25	16.40	15.40
BTB0.851-38PWZDB5-MB42	2*19	14.40	16.05	17.20	16.20
BTB0.851-40PWZDB5-MB42	2*20	15.20	16.85	18.00	17.00
.....	...	...	...	...	...
BTB0.851-80PWZDB5-MB42	2*40	31.20	32.85	34.00	33.00

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE: 0.8 Pitch E型单槽侧插BTB
母座业务图(单高5.1)

PAR BTB0.851-XPWZDB5-MB42

DECIMALS:

ANGLES:

X.: ±0.50

±1°

X.X: ±0.20

X.XX: ±0.10

CUSTOMER COPY

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE 1:1 UNIT: MM

SIZE: A4 SHEET: 1F1 REV: A