



This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission


REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	19/03/17	19/03/17

Electrical data	Requirments	
Impedence	50Ω	
Frequency	DC-6GHz	
Center Contact Resistance	≤3MΩ	
Outer Contact Resistance	≤2MΩ	
Insulation Resistance	≥5000mΩ	
VSWR	1.25:1	
Mechanical & Enviromental	Requirments	
Temperature range	-45℃ ~ +85℃	
Durability	>500 cycles	
Material &plating	Requirments	
Connector parts	Material	Plating
Body	Brass	Gold
Pin Contact	Bronze	Gold
Insulators	Teflon	



Notes:

- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 19/03/17	TITLE: RF Coaxial Connector SMA Female Flange Connector Mount	 成都恒利泰科技有限公司 Chengdu HenryTech Technology co., Ltd			
ENGINEER: L.yu 19/03/17					
APPROVED: W.yi 19/03/17		 DIMENSION IN MILLIMETERS (mm)			
TOLERANCES UNLESS OTHERWISE SPECIFIED: X ±0.50 .X ±0.20 .XX ±0.10 ANGLES ±1°		PART NO: HL-SMA-KFD19B	SIZE: A4	SCALE: N/A	SHEET: 1/1