







ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

Specification:

- ELECTRICAL CHARACTERISTICS
 - CONTACT RESISTANCE: 80 milliohms MAX.
 - INSULATION RESISTANCE: 1,000 Megohms MIN.
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE.
- MECHANICAL CHARACTERISTICS
 - DURABILITY: 5,000 CYCLES
- RoHS 2002/95/EC COMPLIANT.





Pin No.	Pin assignment
PIN1	DAT2
PIN2	CD/DAT3
PIN3	CMD
PIN4	VDD
G1	SWITCH
PIN5	CLK
PIN6	VSS
PIN7	DAT0
PIN8	DAT1



C	SHELL	1	STAINLESS STEEL 0.15t	Ni PLATING
B	CONTACT	9	COPPER ALLOY 0.15t	Gold Flash On Contact Area Tin plated on Solder tail All over Nickel Plated .
A	HOUSING	1	HIGH-TEMPERATURE PLASTIC UL94-V0	BLACK
NO	DESCRIPTION	QTY	MATERIAL	PLATING & COLOR
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD		
DRAWING		TITLE SD卡/存储卡卡座T1.5(插拔式卡) REV. A		
CHECK				
APPROVAL				
TOLERANCES ARE		PART NO. LAIL-TF08-T1.5-B UNITS mm		
30-150	±0.35			
10-30	±0.2	DWG.NO. Projection		
5-10	±0.15			
0-5	±0.1			

ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE



NO. 1




NO. 2



纸箱规格:340*340*300

NO. 4



NO. 3

1. 材质要求:

- 1.1 纸箱的材质为A=B;外形尺寸为34*34*30;
- 1.2 卷盘的材质为PVC,卷盘的外形尺寸为 $\phi 330*30.4$;
- 1.3 卷带的材质为PVC,卷带的外形尺寸为24400*24.00*2.4mm;

2. 包装方式:

- 2.1 将卷带放入包装机后,前空20PCS,后放产品2500PCS,再后空28PCS.
- 2.2 将包装好的产品从包装机上取下并包装好;
- 2.3 把累叠好的11盘叠放入纸箱中共计27.5Kset;
- 2.4 把包装好的成品打包封箱,并在纸箱外贴上标签

COSTOMER DRAWING				LAILIAN 深圳市莱联电子有限公司			
DRAWING		CHECK		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
APPROVAL		TOLERANCES ARE		TITLE	SD卡/存储卡卡座T1.5(插拔式卡)	REV.	A
30-150	±0.35	10-30	±0.2	PART NO.	LAIL-TF08-T1.5-B	UNITS	mm
5-10	±0.15	0-5	±0.1	DWG.NO.		Projection	