







ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



PIN/NO	ASSIGNMENT
C1	VCC
C2	RST
C3	CLK
CD	Detect Switch
C5	GND
C6	VPP
C7	I/O



RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)
RECOMMENDED MATAL MASK T=0.12mm

- ▨ SMT SOLDER AREA
▩ NO PATTERN AND VIA HOLE IN HTIS AREA

NOTES:

1.MATERIAL:

HOUSING: High Temperature Thermoplastic

Terminal:Copper Alloy

Shell: Stainless Steel

2.PLATING:

Terminal:30u" Ni UNDERPLATED OVERALL

G/F PLATED ON CONTACT AREA AND SOLDER AREA

Shell:30u" Ni UNDERPLATED OVERALL

G/F PLATED ON CONTACT AREA AND SOLDER AREA

3.technical speciality:

RATED VOLTAGE: 30V AC MAX.

CURRENT RATING: 0.5A MAX.


INSULATION RESISTANCE:1000MΩ MIN

CONTACT REISTANCE:100mΩ MAX

WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTES

OPERATING TEMPERATURE: -40℃~+85℃ Humidity 80% R.H MAX

4.DIMENSIONS WITH MARK" * "MUST BE MEASURE BY QC AND IPQC




COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	SIM卡卡座T1.25 (自弹式)	REV.	A
30-150	±0.35	PART NO.	LAIL-SIM017-T1.25-T	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO.		Projection	
±3°					

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE


NOTES

1. NUMBER OF CONNECTORS:1500PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY:15000PCS/CARTON

User Direction of Unreeling




COVER TAPE PEELING ANGLE:165°~180°


PEELING FORCE:20~130g

CARRIER TAPE

User Direction of Unreeling



DETAIL B




DETAIL B

10-REEL

4-TRIANGLE PARTITION
380*235*5 K3K

CARTON
342*342*315 K=K



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	SIM卡卡座T1.25（自弹式）	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-SIM017-T1.25-T	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
±3°			DWG.NO.		Projection	