




ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE




~ MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Glod Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

~ SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100M Ω MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C ~ $+105^{\circ}$ C.

※ 【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE: ± 0.05

COSTOMER DRAWING			 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	D-SUB连接器37PIN母针弯插	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-D-SUB37P-01-A-W	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			DWG.NO.		Projection	