

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

MATERIAL:

INSULATOR: HIGH TERMERATURE THERMOPLASTIC,UL 94V-0

CONTACT: COPPER ALLOY

SHELL: SUS

PLATING:

CONTACT: PLATED 50U" NI OVER ALL CONTACT AU 1U

SHELL: PLATED 50U" NI OVERALL

PLATED 1U" AU SELECTIVE CONTACT AREA

ELECTRICAL:

CURRENT RATING: 0.5AMPS MAX

VOLTAGE RATING: 5V AC/DC







AMBIENT TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$ STORAGE TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$

AMBIENT HUMIDITY RANGE: 95% R.H. MAX.

CONTACT RESISTANCE: 100M Ω MAX.INSULATION RESISTANCE: 1000M Ω MIN./500VDCREFLOW PEAK TEMP: 260 $^{\circ}\text{C}$

MATING CYCLES: 5000MIN INSERTIONS

SALT APRAY TIME:48H




PAD AREA

KEEP OUT AREA

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

Circuit Diagram for Detect Switch




MICRO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A
CD	DETECTION SWITCH

COSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD					
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	SIM卡卡座T1.35（自弹式）	REV.	A		
30-150	±0.35	PART NO.	LAIL-SIM04-T1.35-T	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection			
±3°							


ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE





NOTES

1. 每卷包装数量: 1000PCS/每卷
2. 卷带包装方式:




3. 每箱包装数量: 10000PCS/箱

4. 纸箱 350mm*350mm*440mm (内净尺寸), 材质 K=K




纸箱底衬和顶衬各垫一块珍珠棉



将10卷产品放入箱内

外箱标签贴示位置



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	SIM卡卡座T1.35 (自弹式)	REV.	A
30-150	±0.35	PART NO.	LAIL-SIM04-T1.35-T	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO.		Projection	
±3°					