







ROHS



Main technical performance	
Rated electrical load	DC 24V 3A
Contact resistance	≤0.03Ω
Insulation resistance	≥100MΩ DC250V
Pressure resistance	AC 500V 1min
Insertion force	3-20N
Operating temperature range	-20C°~+70C°
service life	5000cycles

4	TERMINAL	1	BRASS	MB:CuSn PLATED
3	HOUSING	1	PBT	BLACK
2	TIP SPRING	1	PHOSPHOR BRONZE	MB:CuSn PLATED
1	CENTER PIN	1	BRASS	MB:CuSn PLATED
LTR	PART NAME	QTY	MATERIAL	REMARK

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING			TITLE		DC电源连接器C2.0带屏蔽（弯插）	REV.	A
CHECK							
APPROVAL			PART NO.		LAIL-DC24-D5.9C2.5-W	UNITS	mm
TOLERANCES ARE							
30-150	±0.35	ANGLE	DWG.NO.		Projection 		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
					±3°		