





技术指标(Technical Index):

- 1.工作温度(Temperature range):-25°C~+85° C.
- 2.适用线规(Apply to gauge):AWG#28~#24
- 3.额定电压(Rated voltage):250V DC/AC (rms).
- 4.额定电流(Rated current):3.0A AC,DC.
- 5.接触电阻(Contact resistance):≤20mΩ.
- 6.耐压值 (Dielectricwithstanding voltage): 800V AC/minute.
- 7.绝缘电阻(Insulation resistance):≥1000MΩ.


材质 (Material)

Housing: LCP UL94 V-0 本色

Terminal: Copper Alloy/Tin Plating



CKT	PART.NO	A	B
2*2	W-2008M04P-0000	2.0	6.0
2*3	W-2008M06P-0000	4.0	8.0
2*4	W-2008M08P-0000	6.0	10.0
2*5	W-2008M10P-0000	8.0	12.0
2*6	W-2008M12P-0000	10.0	14.0
2*7	W-2008M14P-0000	12.0	16.0
2*8	W-2008M16P-0000	14.0	18.0
2*9	W-2008M18P-0000	16.0	20.0
2*10	W-2008M20P-0000	18.0	22.0
2*11	W-2008M22P-0000	20.0	24.0
2*12	W-2008M24P-0000	22.0	26.0
2*13	W-2008M26P-0000	24.0	28.0
2*14	W-2008M28P-0000	26.0	30.0
2*15	W-2008M30P-0000	28.0	32.0
2*16	W-2008M32P-0000	30.0	34.0
2*18	W-2008M36P-0000	34.0	38.0
2*20	W-2008M40P-0000	38.0	42.0



TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO., LTD			
CHECKED:	DATE:	TITLE: 2008SMT-2*XP 卧贴 (PHD 双排)			
DRAWN: LYF	DATE: 2024-5-26	PART. NO.	W-2008MXXP-0000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-2008-0018	REV.	A WD01